

## Balante electronice

### KERN

#### Model ABT

##### Balanta analitica

platanul are  $\varnothing$  80 mm, poate fi conectata la imprimanta inclusiv RS 232.

Calibrarea se face din interior.

Model ABT	Precizie	Greutate maxima	Alimentare
120-4M	0,1 mg	120 g	230 V
220-4M	0,1 mg	220 g	230 V
320-4M	0,1 mg	320 g	230 V
120-5DM	0,01 mg 0,1 mg	42 g 120 g	230 V
220-5DM	0,01 mg 0,1 mg	82 g 220 g	230 V



#### Model MRS

##### Balanta pentru analiza umiditatii

Rezultatele apar in % sau grame, modul incalzire, temperatura si timp. Calibrarea se face din exterior.

Poate avea un set de calibrare a temperaturii.

Model MRS	Precizie	Greutate max	Alimentare
120-3	0,001 g	120 g	230 V



#### Model CDEE

##### Sistem de cantarire

Este format dintr-o balanta de referinta o balanta de cantarire.

Acest sistem ofera avantajul de a folosi fiecare scala individual.

Sistemul de cantarire prezinta interfata seriala RS 232.

Model CDEE	Precizie	Greutate max	Alimentare
35K0.01	-	-	230 V
60K0.1	-	-	230 V
150K0.1	-	-	230 V



### **CE Cimpoaca Electronic SRL**

Sos. Stefan cel Mare, nr. 23, sector 2, Bucuresti

Tel.: 021-2122511, 021-2119996, 0740099959, Fax: 021-2119996

[rolab@cimpoaca.com](mailto:rolab@cimpoaca.com)

[www.cimpoaca.ro](http://www.cimpoaca.ro)

Asociat majoritar

CE Cimpoaca Elektronik GmbH

Stuttgart- Germania